



Physical Test Solutions

Innovative Solutions in Material Test Equipment


High Capacity Impact Testers



IT Series Impact Testers

The **Physical Test Solutions IT Series** of impact testers offers *turn – key solution* packages. No need to decipher what hammers, tools, and other “recommended” accessories have to be ordered, **PTS** has it all included! Furthermore, all **PTS** impact testers offer automatic release and return mechanism, as well as a brake mechanism. All **PTS** impact testers are manufactured in an ISO 9001 certified facility

There are three types of pendulum impact tests; Izod, Charpy and Tensile Impact. The first two are the most common. Typically, Izod tests are most used in low energy applications for plastics and non-metallic materials, whereas Charpy tests are usually seen in high energy tests in metallic materials.



The **IT Series** of high capacity impact testers used to determine the impact characteristics of metals has two main devices; the striking hammer and tooling for Charpy or Izod tests. The impact energy can be seen on a dial, or on a digital display or on a computer. High capacity impact testers are available in capacities of 300 J, 500J and 800J. All **IT Series** high capacity impact testers conform to ASTM E23, ISO148-1983 and GB/T3808-1995

ImpactStar Software

The **ImpactStar Software** operates in a windows environment and combines a user friendly working operation with powerful data acquisition and control capabilities.

The **ImpactStar Software** has the following features:

- ⌚ Full digital control
- ⌚ Individual or Batch Testing Capabilities
- ⌚ Test Curve Analysis 2
- ⌚ Convenient and Practical Parameter Settings
- ⌚ Multilevel Security Management
- ⌚ Versatile Operating Interface
- ⌚ Automatic Program Control
- ⌚ Versatile Test Report Generation
- ⌚ Practical Database Management



ITA Series Impact Testers

The **ITA Series** of impact testers is an analog tester that uses a dial gauge to read the impact energy. The analog method is the oldest form of measurement, and is also the most cost efficient method. The ITA is available in capacities of 300J, 500J and 800J.



Standard Accessories for 300J Model

- ✓ Large Pendulum (300J)
- ✓ Small Pendulum (150J)
- ✓ Span specimen plate (L=40mm)
- ✓ Specimen centering plate (L=40mm)(U, V)
- ✓ Detaching device (S=30mm)
- ✓ Simple-head spanner
- ✓ Inner-hexagon spanner (S=12mm)
- ✓ Anchor bolts M16x300, 4 pieces
- ✓ Grips (including support) R=1mm 1 pair

ITD Series Impact Testers

The **ITD Series** of impact testers feature a digital readout of test results with an LCD remote display. In this model, the pendulum is raised and released automatically.

Standard Accessories for ITD-500J Model

- ✓ LCD display
- ✓ Large hammer: 500 J
- ✓ Small hammer: 250 J
- ✓ Span specimen plate (L=40mm)
- ✓ Specimen centering plate (L=40mm)(U, V)
- ✓ Detacher device (S=30mm)
- ✓ Simple-head spanner
- ✓ Inner-hexagon spanner (S=12mm)
- ✓ Anchor bolts M16x300 (4 pieces)
- ✓ Grips (including support) R=1mm (1 pair)



ITC Series Impact Testers

The **ITC Series** of impact testers' features computer controlled testing and includes the **Impactstar Software**. The main software features are described in page 4. The system has a digital interface card, an optical-electronic pick-up to measure the release angle. The pendulum is raised and released automatically.

Standard Accessories for ITC-800 Model

- ✓ PC Computer
- ✓ ImpactSoft software
- ✓ Large hammer: 800 J
- ✓ Small hammer: 500 J
- ✓ Span specimen plate (L=40mm)
- ✓ Specimen centering plate (L=40mm)(U, V)
- ✓ Detacher device (S=30mm)
- ✓ Simple-head spanner
- ✓ Inner-hexagon spanner (S=12mm)
- ✓ Anchor bolts M16x300 (4 pieces)
- ✓ Grips (including support) R=1mm (1 pair)



ITC-500 shown with optional safety cover.



Specifications	ITA-ITD-ITC-300	ITA-ITD-ITC-500	ITA-TD-ITC-800
Impact energy (J)	150, 300	250, 500	500, 800
Foot Pound	110, 220	184, 368	368, 590
Kilogram-force-meter	15, 30	25, 50	50, 80
Impact velocity (m/s)	5.2	5.4	5.9
Raised angle	150°		
Standard span (mm)	40		
Round angle of jaws (mm)	R1-1.5		
Round angle of striking edge (mm)	R2-2.5		
Size of specimen (mm)	10 x 10 x 55		
Power supply	4 380V , 3 ph, 50Hz, / 220V, 3 ph., 60 HZ,		
Dimensions (mm)	2124 x 600 x 1340	2144 x 736 x 1390	2450 x 1200 x 2455
Net Weight (Kg)	450	650	2300
Display	ITA – Analog, ITD- LCD Monitor, ITC- Computer		

Impact Accessories

L71-UV Notching Machine for Charpy Impact Specimens

This machine is designed to notch specimens used in the impact testing tasks. The L71-UV may cut notch which according to the national standard GB/T229-1994 "Charpy notch Impact Test Method for metal material" on the specimen for only one time. At the same time, it has advantages of high precision, long life, low noise and attractive appearance.

Specifications and Standard Accessories:

- V type notch according to ASTM E23 and ISO148
- U type 2 mm, 3 mm notch according to DIN50115, and 5 mm according to ISO83
- Size of Specimen: 10 mm x 10 mm x 55 mm
- Cutting knife travel: 330 mm
- Cutting speed: 2.6m/min

Dimensions: 460 mm x 610 mm x 1400 mm

Power supply: 240V/60Hz.

Weight: 400kg



Cryostatic Chamber for Impact Specimens


The chamber is designed to prepare Charpy notched Impact Test specimens for low temperature tests. The unit uses compressor cooling technology made up of two sections (Low temperature grade and high temperature grade). It utilizes the heat balance principle and cycle stirring method to achieve constant temperature cooling of impact specimens for reliable performance. When the chamber is connected to the impact tester to perform low temperature impact tests, the specimen can be delivered automatically.

Main Specifications

- ✓ Temperature control range: +30- -35°C
- ✓ Constant temperature accuracy: $\pm 0.5^{\circ}\text{C}$
- ✓ Temperature dropping speed: +30°C - 0°C, +30°C - -20°C, -20°C - -35°C
- ✓ Dimension: 800x510x750 mm
- ✓ Effective working space: 120x120x80 mm
- ✓ Chamber holds more than 60 specimens
- ✓ Specimen dimension: 10x10x55 mm
- ✓ Digital timer; 1 sec -100 minutes 5
- ✓ Cooling media: Alcohol or other
- ✓ Power supply: 110V/220-240V, 50/60 Hz



DT Series Drop Weight Impact Testers



The DT Series drop weight impact testers are suitable for drop weight tear test to various kinds of ferrites, especially to pipeline steel. The unit is equipped with different weights and anvils and can perform other types of impact tests according to customers' special request.

Features

- ⌚ Impact energy is adjusted by lifting height and the number of weights.
- ⌚ The buffer is equipped to absorb the residual energy after breaking the specimen to protect the weight and anvil from destroying.
- ⌚ The unit is equipped with safety features, such as safety net, safe pin for maintenance and hanger locking.
- ⌚ The tester also has a specimen-carrying system, anti-falling device for the specimen, centering set-up to guarantee quick, accurate and reliable tests.



Standard Accessories

1. Impact hammer
2. Specimen-carrying device
3. Anti-falling of mechanism for the specimen
4. Centering device
5. Safety net

Optional Accessories

According to API 5L, the specimen for drop weight impact test should have a V-groove, but this V-groove can not be made by cutting, only by compression. Compression machine for compressing V-groove

Specifications

Model	DT-20000	DT-30000	DT-40000	DT-50000
Maximum energy	20000J	30000 J	40000 J	50000 J
Maximum lifting height	2800 mm	2800mm	2000mm	2000 mm
Maximum impact velocity	7.4 m/s	7.4 m/s	7.6 m/s	7.6 m/s
Curvature radius of weight	R25 mm	R25 mm	R25 mm	R25 mm
Curvature radius of anvil	R25 mm	R25 mm	R25 mm	R25 mm
Hardness of weight and anvil	≥HRC60-65	≥HRC60-65	≥HRC-60-65	≥ HRC60-65
Distance between supports	254 mm	254 mm	254 mm	254 mm
Specimen Centering deviation	≤±1 mm	≤±1 mm	≤ ± 1 mm	≤ ± 1 mm
Indicating deviation of lifting height	≤±1 mm	≤±1 mm	≤ ± 1 mm	≤ ± 1 mm
Dimensions (mm)	1200 x 1400 x 5500	1200 x 1400 x 5500	1300 x 1500 x 6800 mm	1300 x 1500 x 6800

SALES OFFICES

Headquarters

PHYSICAL TEST SOLUTIONS

11952 Lindblade St.
Culver City, CA. 90230
Tel: (310) 736-1901
info@physicaltestsolutions.com
www.physicaltestsolutions.com/

USA

Assurance Technologies, Inc.
Telephone: (630) 550-5000
Sales@atiquality.com

Anderson Electronics, Inc.
Tel. (248) 526-7000
sales@ael-sales.com

Physical Testing Equipment Services
Tel: (401) 944-4760
support@ptes-inc.com

Measure-All, Inc., Ohio
Tel: 1-800-758-2376
sales@measure-all.com

México

Cientec, Guadalajara.
Tel : (33)3817-0140
ventas@cientec.com.mx

Cientec, Mexico.
Tel : (55) 500-59250
centro@cientec.com.mx

Cientec, Bajío
Tel : (442) 290-3819
bajio@cientec.com.mx

Cientec, Monterrey.
Tel : (81) 8334-2073
norte@cientec.com.mx

Cientec, Saltillo
Tel : (844) 140-8749
salttillo@cientec.com.mx

Tecnica Test
Tel: (442) 216-8265
m.saldamando@tecnicatest.com

Quality Lab Systems, Puebla
Tel: (244) 4465349
victor@qualitylab.com.mx

Centro de Servicios Metrológicos S.A. de C.V.
Cd. Juarez, Chi. 32650
cesemet@hotmail.com

Canada

M&L Testing Equipment
Tel: (905) 689-7327
info@mltest.com

Middle East

Egypt

Scientific Trading Co.
Tel : 202-2670-3806
galal_nough@nouh.com.eg

Dubai

BDH MIDDLE EAST LLC
Tel: 971 4 2852211
sanjay@bdhme.com

Saudi Arabia

Saudi Technology & Equipment Company
(SATECH)
Tel: +96614502928
abbas@satech-co.com

Jordan

Elshaktori Trading Establishment
Tel: 962-6-5651057
elshak@nets.com.jo

Latin America

Argentina

Mess s.a.
Tel. 54 11- 5291-0460 / 0461
ventas@messmedicion.com.ar
www.messmedicion.com.ar/

Brazil

Metromec
Tel: 55 11 4735 3819
Lisias.Serra@metromec.com.br
www.metromec.com.br

Colombia

Mave Instrumentacion y Quimicos Ltda
Tel: (571) 757-9907
mave07@telmex.net.co

Chile

Arquimed S.A.
Tel: (56-2) 6346266
jortiz@arquimed.cl

Peru

DIECOM
Tel: 51-12222717
jbustamante@diecomforestry.com

Venezuela

Proyectos Produtec C.A.
Tel: 58 212 761 61 15
corredor@cantv.net

Bolivia

Reguimport - Lab
Tel. +591 22 456 215
gmallean@entelnet.bo

Costa Rica

Suinsa S.A.
Tel:(506)8330-1536
edwar.suinsa@gmail.com

Europe

Italy

NOSELAB ATS s.r.l.
Tel: +039 036240413
info@noselab-ats.com

England

A.J.T. Equipment Limited
Tel: +44 (0) 1384 482 848
admin@ajtequipment.co.uk

Spain

Zaragoza Wap
Tel:976382592
nacho.gonzalez@zaragozawap.com

France

Sodexim
Tel: 33-(0) 326-0291-11
sodexim@sodexim.org

Greece

M.I Priniotakis
S.A. 30-210-
7227719
ikafegidakis@priniotakis.gr

Russia

SPE Monotest LLC
Tel: 7-916-654-9189
105@monotest.ru

Ukraine

ALT Ukraine Ltd
Tel: 380 44 492 72 70
valery.diumin@alt.ua

Israel

Fisher Intl Ltd
Tel: 972-8-934 8455
fisherma@inter.net.il

Poland

COMEF Aparatura Naukowo-Badawcza
Tel:+48 32 203 41 49
grzegorz@comef.com.pl

Estonia

Laboritugi OÜ
Tel: 3725249849
laboritugi@laboritugi.ee

Romania

SC RedoxLab SRL
Tel. 004-0264-416427
glodan.mihai@redox.com.ro

Asia

China

Earth Products China Ltd.
Tel: 852-39654890
carmenli@epc.com.hk

India

Unitestmac Systems Ltd.
Tel:91-11-25894580 / 25894782
sales@unitestmac.com

Thailand

Max Value Technologies
Tel. : 66 2 717-7199
maxvalue@asiaaccess.net.th

Malaysia

Dutech Scientific (M) Sdn. Bhd.
Tel: 6 03-7956 7861
pau@dutech-inst.com

Korea

Fine T&S Co.,Ltd
harryfin@chol.com
Telephone: +82-2-2244-9584

Indonesia

CV Trimitra Tehnik
Tel (62) 21-591-3967
cv_trimitra@yahoo.com

Singapore

Skyray Instruments
Tel. (65) 64823491
taygi@sigmet.com.sg

Vietnam

Top Technology JSC
Tel: 84 8 2842405
t-tech@viettel.vn

Africa

Nigeria

MD-Mudiame
www.mudiame.com